

S E N S O R Y

Application	Roller Panel
Composition	100% Polyester
Width	290cm 114 inches
Weight	83 gsm
Roll Size	35m 38yd
Care Instructions	Do not allow dust to accumulate. Regularly gently vacuum with appropriate attachment. Do not wash. Do not dry clean. Warm iron if needed. Test in inconspicuous area with mild detergent solution prior to spot cleaning. Do not allow blind to become fully wet, use damp cloth only.

Also available as a Sheer Drapery Range - Sensory



WWW.WILSONFABRICS.COM.AU

WWW.WILSONFABRICS.COM

WHY WILSON FABRICS?

FADE
RESISTANT

Stringently tested for colourfastness to light, ensuring they will stand the test of time.



Australian Standards only.
AS1530.2 Results available upon request.

